

MPA-Pyrometer
8-Polig
8-pin

Länge 2,5 m
length 2,5m

12-polig
12-pin

Belegung
Configuration

Pol
contacts

Funktion
function

weiß <i>white</i>	an 1 <i>at 1</i>	+24 V DC <i>+24 V DC</i>
braun <i>brown</i>	an 2 <i>at 2</i>	Schalt ein- / ausgang 1 <i>Digital in- / output 1</i>
grün <i>green</i>	an 3 <i>at 3</i>	Stromausgang 2 <i>Analogue output 2</i>
gelb <i>yellow</i>	an 4 <i>at 4</i>	Stromausgang 1 <i>Analogue output 1</i>
grau <i>grey</i>	an 5 <i>at 5</i>	Serielle Schnittstelle RS485 (A) <i>Serial interface RS485 (A)</i>
rosa <i>pink</i>	an 6 <i>at 6</i>	Serielle Schnittstelle (B) <i>Serial interface (B)</i>
blau <i>blue</i>	an 7 <i>at 7</i>	Schalt ein- / ausgang 2 <i>Digital in- / output 2</i>
rot <i>red</i>	an 8 <i>at 8</i>	GND <i>GND</i>

Schirm durchgängig an Verschraubung
Shield constantly at screw connection

Gewicht: 0.620 Kg
Weight: 0.620 Kg

Seite 1 von 1
Page 1 of 1



- Headquarters
- Sales and Service Center
- Sales abroad



Keller HCW GmbH
Infrared Temperature Solutions (ITS)
Carl-Keller-Straße 2-10
49479 Ibbenbüren-Laggenbeck
Germany

www.keller.de/its
Tel. +49 (0) 5451 850
Fax +49 (0) 5451 85412
its@keller.de

Distributor



INOR Transmitter Oy
Unikkotie 13
FI-01300 Vantaa
Puhelin +358 10 4217900
Faksi +358 10 4217901
myynti@inor.fi